



G



F



E

D



C

B

A

## SPECIFICATIONS

Current Rating: 1.5 Amps  
 Insulation Resistance: 1000M $\Omega$ , Min  
 Contact Resistance: 20m $\Omega$ , Max  
 Withstanding Voltage: AC 500V  
 Operation Temperature: -40° to +105°  
 Contact Material: Brass  
 Standard: PA6T  
 Insulator Material: Polyester (UL 94V-0)  
 Contact Plating: Gold Flash  
 Max. Processing Temp: 240° C for 30–60 seconds  
 (260° C for 5 seconds)



RECOMMEND P. C. B. LAYOUT  
 PCB TOLERANCE: ±0.05 (TOP VIEW)



深圳市首韩科技有限公司

UNLESS OTHERWISE SPECIFIED TOLERANCE

X : ±0.30 X° : ±5°

X. X : ±0.25 X. X° : ±1°

X. XX : ±0.20 X. XX° : ±0.5°

DRAWN NAME: SH-JN2.0-2-8P-Z-H.4

SIZE	A4	SCALE	N:1	PROUCT NO.		PAGE	1/1
REV	A	UNIT	mm	PROJECT			
DRAW:	李春风	2022/04/30	CHECKED:	钟华华	2022/04/30	APPROVED:	罗孝金