





SPECIFICATIONS

Current Rating: 1.5 Amps  
Insulation Resistance: 1000M $\Omega$ , Min  
Contact Resistance: 20m $\Omega$ , Max  
Withstanding Voltage: AC 500V  
Operation Temperature: -40° to +105°  
Contact Material: Brass  
Standard: PA6T  
Insulator Material: Polyester (UL 94V-0)  
Contact Plating: Gold Flash  
Max. Processing Temp: 240° C for 30-60 seconds  
(260° C for 5 seconds)



RECOMMEND P. C. B LAYOUT  
PCB TOLERANCE:  $\pm 0.05$  (TOP VIEW)

| No. of | DIM. A | DIM. B | No. of | DIM. A | DIM. B | No. of | DIM. A | DIM. B | No. of | DIM. A | DIM. B |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 6      | 4.00   | 8.60   | 24     | 22.00  | 26.60  | 42     | 40.00  | 44.60  | 60     | 58.00  | 62.60  |
| 8      | 6.00   | 10.60  | 26     | 24.00  | 28.60  | 44     | 42.00  | 46.60  | 62     | 60.00  | 64.60  |
| 10     | 8.00   | 12.60  | 28     | 26.00  | 30.60  | 46     | 44.00  | 48.60  | 64     | 62.00  | 66.60  |
| 12     | 10.00  | 14.60  | 30     | 28.00  | 32.60  | 48     | 46.00  | 50.60  | 66     | 64.00  | 68.60  |
| 14     | 12.00  | 16.60  | 32     | 30.00  | 34.60  | 50     | 48.00  | 52.60  | 68     | 66.00  | 70.60  |
| 16     | 14.00  | 18.60  | 34     | 32.00  | 36.60  | 52     | 50.00  | 54.60  | 70     | 68.00  | 72.60  |
| 18     | 16.00  | 20.60  | 36     | 34.00  | 38.60  | 54     | 52.00  | 56.60  |        |        |        |
| 20     | 18.00  | 22.60  | 38     | 36.00  | 40.60  | 56     | 54.00  | 58.60  |        |        |        |
| 22     | 20.00  | 24.60  | 40     | 38.00  | 42.60  | 58     | 56.00  | 60.60  |        |        |        |



韩下®  
HANXIA

深圳市韩下电子有限公司

|                                      |              |            |                   |                                  |    |            |     |
|--------------------------------------|--------------|------------|-------------------|----------------------------------|----|------------|-----|
| UNLESS OTHERWISE SPECIFIED TOLERANCE |              |            |                   | DRAWN NAME: HX IDC200-2-03-Z-6.4 |    |            |     |
| X                                    | : $\pm 0.30$ | X°         | : $\pm 5^\circ$   | SIZE                             | A4 | SCALE      | N:1 |
| X.X                                  | : $\pm 0.25$ | X.X°       | : $\pm 1^\circ$   | REV                              | A  | UNIT       | mm  |
| X.XX                                 | : $\pm 0.20$ | X.XX°      | : $\pm 0.5^\circ$ | PROJECT                          |    |            |     |
| DRAW: 黄彬                             |              | 2022/04/30 |                   | CHECKED: 张伟                      |    | 2022/04/30 |     |
|                                      |              |            |                   | APPROVED: 罗小春                    |    | 2022/04/30 |     |