





G



## SPECIFICATIONS

Current Rating: 1.5 Amps  
 Insulation Resistance: 1000M $\Omega$ , Min  
 Contact Resistance: 20m $\Omega$ , Max  
 Withstanding Voltage: AC 500V  
 Operation Temperature: -40° to +105°  
 Contact Material: Brass  
 Standard: PA6T  
 Insulator Material: Polyester (UL 94V-0)  
 Contact Plating: Gold Flash  
 Max. Processing Temp: 240° C for 30–60 seconds  
 (260° C for 5 seconds)

E



RECOMMEND P. C. B. LAYOUT  
 PCB TOLERANCE: ±0.05 (TOP VIEW)

A

SH 首韩		深圳市首韩科技有限公司						
UNLESS OTHERWISE SPECIFIED TOLERANCE		DRAWN NAME: SH-JN2.0-2-9P-W-H6.4						
X : ±0.30	X° : ±5°	SIZE	A4	SCALE	N:1	PROUCT NO.		
X. X : ±0.25	X. X° : ±1°	REV	A	UNIT	mm	PROJECT		
X. XX: ±0.20	X. XX° : ±0.5°	DRAW:	李春风	CHECKED:	钟华华	2022/04/30	APPROVED:	罗孝金
							PAGE	1/1

1

5

6

7

8

9

G

F

E

D

C

B

A