


G



## SPECIFICATIONS

Current Rating: 1.5 Amps  
 Insulation Resistance: 1000M $\Omega$ , Min  
 Contact Resistance: 20m $\Omega$ , Max  
 Withstanding Voltage: AC 500V  
 Operation Temperature: -40° to +105°  
 Contact Material: Brass  
 Standard: PA6T  
 Insulator Material: Polyester (UL 94V-0)  
 Contact Plating: Gold Flash  
 Max. Processing Temp: 240° C for 30–60 seconds  
 (260° C for 5 seconds)

F




E

D

C

B

A



RECOMMEND P. C. B. LAYOUT  
 PCB TOLERANCE: ±0.05 (TOP VIEW)



深圳市首韩科技有限公司

UNLESS OTHERWISE SPECIFIED TOLERANCE

X : ±0.30 X° : ±5°

X. X : ±0.25 X. X° : ±1°

X. XX : ±0.20 X. XX° : ±0.5°

DRAWN NAME: SH-JN2.0-2-3P-Z-H6.4

SIZE	A4	SCALE	N:1	PROUCT NO.
------	----	-------	-----	------------

REV	A	UNIT	mm	PROJECT
-----	---	------	----	---------

PAGE	1/1
------	-----

DRAW:	李春风	2022/04/30	CHECKED:	钟华华	2022/04/30	APPROVED:	罗孝金	2022/04/30
-------	-----	------------	----------	-----	------------	-----------	-----	------------

1

2

3

4

5

6

7

8

9

G

F

E

D

C

B

A