





RoHS



技术要求:

- 1.打铜底0.5-1 μ m,镍2-2.5 μ m, 镀雾锡3-5 μ m。
- 2.铆好后不得有松动现象。
- 3.插脚尖部符合可焊性要求。
- 4.螺纹需符合通止规/止针要求。
- 5.螺纹扭矩: 1.0Nm.
- 6.额定电流: 50A.

>30.±0.4	X.°±	PART NO: T44080080-2700		XFCN 兴飞连接器		
6-30±0.3	.X°±					
0-6±0.2	.XX°±	TITLE: PCB SOLDERING TERMINAL		0769-82001899		
ANGLES±1°	.XXX°±			www.xfconn.com		
UNITS:	mm			DWG NO: /		
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN		APPD	Chen ZhiQiang			
		CHKD	Liu Wei	VIEW		
		DRAW	Chen HongJiang	SCALE	SHEET	REV
		DATE	2025.07.15	NONE	1/1	A1

1	插脚		H62 (Y2)	1
序号	名称	零件编号	材质	数量