




G
F
E
D
C
B
A

SPECIFICATIONS

Current Rating: 1.5 Amps
 Insulation Resistance: 1000M Ω , Min
 Contact Resistance: 20m Ω , Max
 Withstanding Voltage: AC 500V
 Operation Temperature: -40° to +105°
 Contact Material: Brass
 Standard: PA6T
 Insulator Material: Polyester (UL 94V-0)
 Contact Plating: Gold Flash
 Max. Processing Temp: 240° C for 30–60 seconds
 (260° C for 5 seconds)



RECOMMEND P. C. B. LAYOUT
 PCB TOLERANCE: ±0.05 (TOP VIEW)



深圳市首韩科技有限公司

UNLESS OTHERWISE SPECIFIED TOLERANCE

X : ±0.30 X° : ±5°

X. X : ±0.25 X. X° : ±1°

X. XX : ±0.20 X. XX° : ±0.5°

DRAWN NAME: SH-JN2.0-2-5P-Z-H6.4

SIZE	A4	SCALE	N:1	PROUCT NO.	
REV	A	UNIT	mm	PROJECT	
DRAW:	李春风	2022/04/30	CHECKED:	钟华华	2022/04/30
			APPROVED:	罗孝金	2022/04/30