



1 2 3 4 5 6 7 8 9


G



F




E



D

SPECIFICATIONS

Current Rating: 1.5 Amps
 Insulation Resistance: $1000M\Omega$, Min
 Contact Resistance: $20m\Omega$, Max
 Withstanding Voltage: AC 500V
 Operation Temperature: -40° to $+105^\circ$
 Contact Material: Brass
 Standard: PA6T
 Insulator Material: Polyester (UL 94V-0)
 Contact Plating: Gold Flash
 Max. Processing Temp: 240° C for 30–60 seconds
 $(260^\circ$ C for 5 seconds)



RECOMMEND P. C. B. LAYOUT
 PCB TOLERANCE: ± 0.05 (TOP VIEW)



深圳市首韩科技有限公司

UNLESS OTHERWISE SPECIFIED TOLERANCE

X : ± 0.30 X° : $\pm 5^\circ$

X. X : ± 0.25 X. X° : $\pm 1^\circ$

X. XX : ± 0.20 X. XX° : $\pm 0.5^\circ$

DRAWN NAME: SH-JN2.0-2-5P-W-H6.4

SIZE	A4	SCALE	N:1	PROUCT NO.	
------	----	-------	-----	------------	--

REV	A	UNIT	mm	PROJECT		PAGE	1/1
-----	---	------	----	---------	--	------	-----

DRAW:	李春风	2022/04/30	CHECKED:	钟华华	2022/04/30	APPROVED:	罗孝金	2022/04/30
-------	-----	------------	----------	-----	------------	-----------	-----	------------

1

2

3

4

5

6

7

8

9

G

F

E

D

C

B

A