






1 2 3 4 5

REV.	ECN	DESCRIPTION		MDF'D	DATE
		新订图面			
		PIN数	型号	尺寸 (mm)	
				A	B
2	ZH1.5-2Y	1.5	4.45		
3	ZH1.5-3Y	3.0	5.95		
4	ZH1.5-4Y	4.5	7.45		
5	ZH1.5-5Y	6.0	8.95		
6	ZH1.5-6Y	7.5	10.45		
7	ZH1.5-7Y	9.0	11.95		
8	ZH1.5-8Y	10.5	13.45		
9	ZH1.5-9Y	12.0	14.95		
10	ZH1.5-10Y	13.5	16.45		
11	ZH1.5-11Y	15.0	17.95		
12	ZH1.5-12Y	16.5	19.45		
13	ZH1.5-13Y	18.0	20.95		
14	ZH1.5-14Y	19.5	22.45		
15	ZH1.5-15Y	21.0	23.95		
16	ZH1.5-16Y	22.5	25.45		
17	ZH1.5-17Y	24.0	26.95		
18	ZH1.5-18Y	25.5	28.45		
19	ZH1.5-19Y	27.0	29.95		
20	ZH1.5-20Y	28.5	31.45		

线型：1571 28#



剥皮镀锡



技术要求:

- 标识清晰可见，表面不得有划痕，裂纹，起泡，污损，毛刺等；
- 无明显影响使用功能和接触性能的缺陷
- 材料：塑料PA66
- 额电电流：0.5A AC, DC
- 额电电压：30V AC, DC
- 接触电阻： $\leq 20m\Omega$
- 绝缘电阻： $\geq 100M\Omega$
- 应用线型：AWG #28 (1571)
- 温度范围：-25°C to +85°C

页码 (SHEET)	1	单位 (UNIT) : MM
版本 (REV)	A1	比例 (SCALE) 1:1
日期 (DATE)	2024.3.20	
设计 (DESIGN)	黄彬	未注 公差 TOLERANCE UNSPECIFIED
审核 (CHECKED)	张伟	$> XX \pm 3$ $> X \pm 1$ $0.X \pm 0.20$ $0.XX \pm 0.15$
核准 (APPROVED)	罗小春	

1 2 3 4 5