



SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω , Min
Contact Resistance: 20m Ω , Max
Withstanding Voltage: AC 500V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240° C for 30-60 seconds
(260° C for 5 seconds)

RECOMMEND P. C. B LAYOUT
PCB TOLERANCE: ± 0.05 (TOP VIEW)



深圳市首韩科技有限公司

UNLESS OTHEWIXE SPECIFIED TOLERANCE

X	: ±0.30	X°	: ±5°
X.X	: ±0.25	X.X°	: ±1°
X.XX	: ±0.20	X.XX°	: ±0.5°

DRAWN NAME:	SH-JN2.0-2-4P-Z-H6.4
-------------	----------------------

SIZE	A4	SCALE	N:1	PROUCT NO.				
REV	A	UNIT	mm	PROJECT			PAGE	1/1
0 CHECKED:		钟华华	2022/04/30	APPROVED:	罗孝金		2022/04/30	

DRAW:	李春风	2022/04/30	CHECKED:	钟华华	2022/04/30	APPROVED:	罗孝金	2022/04/30
-------	-----	------------	----------	-----	------------	-----------	-----	------------