




RoHS

M5-6H

PCB LAYOUT

技术要求:


- 1.打铜底0.5-1 μ m,镍2-2.5 μ m, 镀哑锡3-5 μ m。
- 2.铆好后不得有松动现象。
- 3.插脚尖部符合可焊性要求。
- 4.螺纹需符合通止规/止针要求。
- 5.螺纹扭矩: 2.0Nm.
- 6.额定电流: 80A.

Ordering Code:

TS54010B-R
1 2

- 1.序列号
- 2.R=编带卷装

载带图



包装说明:

- 1.把成品贴麦拉包入卷盘中, 每盘装500PCS,卷盘上贴标签

>30.±0.4	X.°±	PART NO: TS54010B-R		XFCN 兴飞连接器				
6-30±0.3	.X°±							
0-6±0.2	.XX°±							
ANGLES±1°	.XXX°±							
UNITS:	mm	TITLE: PCB SOLDERING TERMINAL		0769-82001899				
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN				www.xfconn.com				
		APPD		Chen ZhiQiang		DWG NO: /		
		CHKD		Liu Wei		VIEW		
		DRAW		Chen HongJiang		SCALE	SHEET	REV
		DATE		2025.08.22		NONE	1/1	A1

1	插脚		H62 (Y2)	1
序号	名称	零件编号	材质	数量