

1

2

3

4

5





红  
黑

200mm

3mm

线型：1007 22#

剥皮镀锡



REV.	ECN	DESCRIPTION		MDF'D	DATE
		线数 Poles	型号 Type		
		A	B		
2	VH3.96-2Y	3.96	8.52		A
3	VH3.96-3Y	7.92	12.48		
4	VH3.96-4Y	11.88	16.44		
5	VH3.96-5Y	15.84	20.4		
6	VH3.96-6Y	19.8	24.36		
7	VH3.96-7Y	23.76	28.32		
8	VH3.96-8Y	27.72	32.28		
9	VH3.96-9Y	31.68	36.24		
10	VH3.96-10Y	35.64	40.2		
11	VH3.96-11Y	39.6	44.16		
12	VH3.96-12Y	43.56	48.12		
13	VH3.96-13Y	47.52	52.08		
14	VH3.96-14Y	51.48	56.04		
15	VH3.96-15Y	55.44	60.0		
16	VH3.96-16Y	59.4	63.96		

#### 技术要求:

- 标识清晰可见, 表面不得有划痕, 裂纹, 起泡, 污损, 毛刺等;
- 无明显影响使用功能和接触性能的缺陷
- 材料: 塑料PA66
- 额电电流: 1.5A AC, DC
- 额电电压: 300V AC, DC
- 接触电阻:  $\leq 20\text{m}\Omega$
- 绝缘电阻:  $\geq 100\text{M}\Omega$
- 应用线型: AWG #22 (1007)
- 温度范围: -25°C to +85°C

 **深圳市韩下电子有限公司**

品名 (ITEM NO) HX VH3.96-2P DT 200mm 22AWG

料号 (PART NO)

图号 (DWG NO)

页码 (SHEET)	1	单位 (UNIT): MM
版本 (REV)	A1	比例 (SCALE) 1:1
日期 (DATE)	2024.3.20	未注公差 TOLERANCE UNSPECIFIED
设计 (DESIGN)	黄彬	
审核 (CHECKED)	张伟	
核准 (APPROVED)	罗小春	

1

2

3

4

5