





G



SPECIFICATIONS

Current Rating: 1.5 Amps
 Insulation Resistance: 1000M Ω , Min
 Contact Resistance: 20m Ω , Max
 Withstanding Voltage: AC 500V
 Operation Temperature: -40° to +105°
 Contact Material: Brass
 Standard: PA6T
 Insulator Material: Polyester (UL 94V-0)
 Contact Plating: Gold Flash
 Max. Processing Temp: 240° C for 30–60 seconds
 (260° C for 5 seconds)

E



RECOMMEND P. C. B. LAYOUT
 PCB TOLERANCE: ±0.05 (TOP VIEW)

B

A

SH 首韩 SHOUHAN		深圳市首韩科技有限公司					
		DRAWM NAME: SH-JN2.0-2-6P-W-H6.4					
UNLESS OTHERWISE SPECIFIED TOLERANCE		SIZE	A4	SCALE	N:1	PROUCT NO.	
X : ±0.30 X° : ±5°		REV	A	UNIT	mm	PROJECT	
X. X : ±0.25 X. X° : ±1°		DRAW:	李春风	CHECKED:	钟华华	APPROVED:	罗孝金
X. XX: ±0.20 X. XX° : ±0.5°			2022/04/30		2022/04/30		2022/04/30
						PAGE	1/1