



深圳市兴华鑫电子科技有限公司

Shenzhen xinghuaxin Electronic Technology Co., Ltd

承認書

SPECIFICATION FOR APPROVAL

客戶 (Customer) : _____

客戶料號 (Customer P/N) : _____

興華鑫型號 (Supplier P/N) : HC2455-L55MM

產品名稱 (Description) : 蜂鳴器 (Buzzer)

產品規格 (Specification) : 24*5.5MM 4.0KHZ 无源压电式

客戶承認欄 (Customer Authorization Signature)	深圳市興華鑫電子科技有限公司 承認欄 (Supplier Audit)		
	審核	檢查	制作
	唐國興	唐玉來	吳銀娟
日期: 2022 年 04 月 19 日			
版次: A			

声音让生活更精彩!

地址: 深圳市宝安区新安街道新乐社区新乐路 88 号厂房四层

TEL: 0755-27892904

E-mail: jacky.tang@jsxhxdz.com

Http: www.jsxhxdz.com

产品参数

Customer:	Part No:		
Product: Piezoelectric Buzzers	XA Part No:XHxDZ-HC2455引线		
Technical Terms			
Resonant Frequency (KHZ)	4 ± 0.5		
Rated Voltage (V_{P-P})	5.0		
Operating Voltage (V_{P-P})	1~25		
Max. Current Consumption at Rated Voltage (mA)	3.0		
Capacitance at 100Hz (nF)	$15 \pm 30\%$		
Min. Sound Output at 10cm at Rated Voltage (dB)	85		
Operating Temperature (°C)	-20~+70		
Storage Temperature (°C)	-30~+70		
Housing Material	ABS(Black)		
Buzzer	Soldering Parameter		
Soldering process	Temp.(°C)	Time(Sec.)	Times
Inclusive Lead	Reflow soldering	230 ± 10	above 170°C time 40~70
	Wave soldering	245 ± 5	3~6
	Manual soldering	330 ± 10	1~2
Lead Free	Reflow soldering	245 ± 15	above 180°C time 40~70
	Wave soldering	260 ± 5	4~8
	★ Manual soldering	350 ± 10	1~3

APPEARANCE DRAWING

Tol : ± 0.5 Unit: mm

