




REV	ECN NO.	DESRPTION	DESIGN	APPROVAL	DATE
A1	NEW	新版发行			2025.08.21

SPECIFICATIONS

- Current rating: 2A
- Temperature range: -40°C ~ +105°C
- Insulation resistance: 1000MΩ Min.
- Withstanding voltage: 500V AC/ minute.
- Contact resistance: 20mΩ Max.

Material:
Insulator Material:PA6T (UL 94V-0)
Contact Material:Brass
Plating:Matte Tin or gold plated over Nickel
Mate with XFCN PZ200 Double Row series

Ordering Code:
PM200VS-12-XX-H43-W45
1 2

1.序列号
2.Pin位数: 2x2=04P
2x10=20P
2x20=40P

No.of PIN/ROW	Dimension	
	A	B
2*02	2.00	4.40
2*03	4.00	6.40
2*04	6.00	8.40
2*05	8.00	10.40
2*06	10.00	12.40
2*07	12.00	14.40
2*08	14.00	16.40
2*09	16.00	18.40
2*10	18.00	20.40
2*11	20.00	22.40
2*12	22.00	24.40
2*13	24.00	26.40
2*14	26.00	28.40
2*15	28.00	30.40
2*16	30.00	32.40
2*17	32.00	34.40
2*18	34.00	36.40
2*19	36.00	38.40
2*20	38.00	40.40
2*21	40.00	42.40
2*22	42.00	44.40
2*23	44.00	46.40
2*24	46.00	48.40
2*25	48.00	50.40
2*26	50.00	52.40
2*27	52.00	54.40
2*28	54.00	56.40
2*29	56.00	58.40
2*30	58.00	60.40
2*31	60.00	62.40
2*32	62.00	64.40
2*33	64.00	66.40
2*34	66.00	68.40
2*35	68.00	70.40
2*36	70.00	72.40
2*37	72.00	74.40
2*38	74.00	76.40
2*39	76.00	78.40
2*40	78.00	80.40

X.±0.50	X.°±	PART NO: PM200VS-12-XX-H43-W45		XFCN 兴飞连接器				
.X±0.25	.X°±							
.XX±0.15	.XX°±	TITLE: 2.00mm Female Header Connectors		0769-82001899				
.XXX±0.10	.XXX°±			www.xfconn.com				
UNITS:	mm	APPD		Chen ZhiQiang		DWG NO: /		
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN								
		CHKD		Liu Wei		VIEW		
		DRAW		Chen HongJiang		SCALE	SHEET	REV
		DATE		2025.08.21		NONE	1/1	A1