




1	2	3	4	5
		REV.	ECN	DESCRIPTION
				MDF'D DATE



线数 Poles	型号 Type	尺寸Size (mm)		
		A	B	C (大)
2	XHB2.5-2Y	2.5	7.3	5.1
3	XHB2.5-3Y	5.0	9.8	5.1
4	XHB2.5-4Y	7.5	12.3	5.1
5	XHB2.5-5Y	10.0	14.8	7.6
6	XHB2.5-6Y	12.5	17.3	10.1
7	XHB2.5-7Y	15.0	19.8	12.6
8	XHB2.5-8Y	17.5	22.3	15.1
9	XHB2.5-9Y	20.0	24.8	17.6
10	XHB2.5-10Y	22.5	27.3	20.1
11	XHB2.5-11Y	25.0	29.8	22.6
12	XHB2.5-12Y	27.5	32.3	25.1
13	XHB2.5-13Y	30.0	34.8	27.6
14	XHB2.5-14Y	32.5	37.3	30.1
15	XHB2.5-15Y	35.0	39.8	32.6
16	XHB2.5-16Y	37.5	42.3	35.1

技术要求:

- 标识清晰可见，表面不得有划痕，裂纹，起泡，污损，毛刺等；
- 无明显影响使用功能和接触性能的缺陷；
- 材料：塑料PA66
- 额电电流：1.0A AC, DC
- 额电电压：300V AC, DC
- 接触电阻： $\leq 20m\Omega$
- 绝缘电阻： $\geq 100M\Omega$
- 应用线型：AWG #24 (1007)
- 温度范围：-25°C to +85°C

页码 (SHEET)	1	单位 (UNIT) : MM
版本 (REV)	A1	比例 (SCALE) 1:1
日期 (DATE)	2024.3.20	○ ◀
设计 (DESIGN)	黄彬	未注公差 TOLERANCE UNSPECIFIED
审核 (CHECKED)	张伟	$> XX \pm 3$ $> X \pm 1$ $0.X \pm 0.20$ $0.XX \pm 0.15$
核准 (APPROVED)	罗小春	