



P.C.B LAYOUT

Specification

Insulator Material: Polysetr, UL94V-0

Nylon-6T

Contact Material: Brass

Current Rating : 1Amp

Insulation Resistace : 1000MΩ Min.

Dielectric withstanding Voltage: AC 500V

Operation Temperature : -40℃ -- +105℃

TOLERANCE TABLE	
.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:	C _{kmtw} 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO., LTD					
CHECKED:	DATE:	TITLE: 210-1SMT-2*6P 塑高1.0 W=5.3 PA=4.0mm					
DRAWN: LYF	DATE: 2008-07-23	PART. NO.	B-2101N12P-R111				
		UNIT	mm	SCALE	free	⊕	≡
		FILE NO.	Ckmtw-210-10027		REV.	A	