






■ SPECIFICATIONS

- ◆ Rated voltage: 125V DC,AC(rms)
- ◆ Rated Current: 1A
- ◆ Withstand voltage: 500V AC/min.
- ◆ Working Temp : -25°C ~ +85°C
- ◆ Insulation resistance: ≥100 MΩ
- ◆ Contact resistance: ≤20mΩ

No. of Contacts	DIMENSIONS		
	A	B	C
2P	7.50	4.40	1.25
3P	8.75	5.65	2.50
4P	10.0	6.90	3.75
5P	11.25	8.15	5.00
6P	12.50	9.40	6.25
7P	13.75	10.65	7.50
8P	15.00	11.90	8.75
9P	16.25	13.15	10.0
10P	17.50	14.40	11.25
11P	18.75	15.65	12.50
12P	20.00	16.90	13.75
13P	21.25	18.15	15.00
14P	22.50	19.40	16.25
15P	23.75	20.65	17.50
16P	25.00	21.90	18.75
17P	26.25	23.15	20.00
18P	27.50	24.40	21.25
19P	28.75	25.65	22.50
20P	30.00	26.90	23.75



PCB Layout

③	Solder Tab	—	2	Brass	Sn-PLATED	—
②	PIN	—	—	Phosphor bronze	Sn-PLATED	—
①	Base	—	1	LCP	Beige	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE				
DRAWN		LIUCAN	2023.2.3				
CHECKED					TITLE:	Bar Connector Series	
APPROVALS					PART NO.	1.25T-nP-WT	
D.	TOLERANCES ARE		30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1
			10~30	±0.20			
			5~10	±0.15			
			~ 5	±0.10			
			±2'		DRAWING NO.	_____	PROJ: 
							SHEET 1 OF 1

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.