


P. C. B. LAYOUT

Specification

Insulator Material: Polysetr, Nylon-6T

Contact Material: Phosphor Bronze(C5191)

Current Rating : 1Amp

Insulation Resistace : 1000MΩ Min.

Dielectric withstanding Voltage:AC 500V

Operation Temperature : -40℃ -- +105℃

TOLERANCE TABLE

. 0	±0. 20
. 00	±0. 10
. 000	±0. 05

APPROVED:	DATE:	C _{kmtw} 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO., LTD					
CHECKED:	DATE:	TITLE: 220-1SMT-2*7P H=4.3mm W=4.8mm					
DRAWN: LYF	DATE: 2008-4-17	PART. NO.	B-2201N14P-B221				
		UNIT	mm	SCALE	free	☉	≡
		FILE NO.	Ckmtw-220-10004		REV.	A	