


P. C. B. LAYOUT

Specification

Insulator Material: Polysetr,UL94V-0

Nylon-6T

Contact Material: Phosphor Bronze (C5191)

Current Rating : 1Amp

Insulation Resistace : 1000M Ω Min.

Dielectric withstanding Voltage:AC 500V

Operation Temperature : -40 $^{\circ}$ C -- +105 $^{\circ}$ C

TOLERANCE TABLE

.0	± 0.20
.00	± 0.10
.000	± 0.05

APPROVED:	DATE:	C _{kmtw} 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO., LTD					
CHECKED:	DATE:	TITLE: 220-1SMT-2*6P H=3.4mm W=4.8mm					
DRAWN: LYF	DATE: 2018-07-23	PART. NO.	B-2201N12P-R120				
		UNIT	mm	SCALE	free		
		FILE NO.	Ckmtw-220-10003		REV.	A	