



P.C.B LAYOUT

Specification

Insulator Material: Polysetr,UL94V-0
Nylon-6T

Contact Material: Brass

Current Rating : 1Amp

Insulation Resistace : 1000MΩ Min.

Dielectric withstanding Voltage:AC 500V

Operation Temperature : -40℃ -- +105℃

TOLERANCE TABLE	
.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:	C _{kmtw} 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO., LTD					
CHECKED:	DATE:	TITLE: 210-1SMT-2*6P 塑高1.0 W=5.5 PA=3.0mm					
DRAWN: LYF	DATE: 2008-07-23	PART. NO.		B-2101N12P-R110			
		UNIT	mm	SCALE	free		
		FILE NO.		Ckmtw-210-10003		REV.	A