



G
F
E
D
C
B
A

深圳市首韩科技有限公司

UNLESS OTHERWISE SPECIFIED TOLERANCE

X : ±0.30 X° : ±5°

X. X : ±0.25 X. X° : ±1°

X. XX : ±0.20 X. XX° : ±0.5°

DRAWN NAME: SH-JN2.0-2-2P-Z-H6.4

SIZE	A4	SCALE	N:1	PROUCT NO.
------	----	-------	-----	------------

REV	A	UNIT	mm	PROJECT
-----	---	------	----	---------

DRAW:	李春风	2022/04/30	CHECKED:	钟华华	2022/04/30	APPROVED:	罗孝金	2022/04/30
-------	-----	------------	----------	-----	------------	-----------	-----	------------

SPECIFICATIONS

Current Rating: 1.5 Amps

Insulation Resistance: 1000MΩ, Min

Contact Resistance: 20mΩ, Max

Withstanding Voltage: AC 500V

Operation Temperature: -40° to +105°


Contact Material: Brass

Standard: PA6T

Insulator Material: Polyester (UL 94V-0)

Contact Plating: Gold Flash

Max. Processing Temp: 240° C for 30–60 seconds
(260° C for 5 seconds)



RECOMMEND P. C. B. LAYOUT

PCB TOLERANCE: ±0.05 (TOP VIEW)