



PCB LAYOUT



SPECIFICATION:

Current Rating:1.5AMP

Contact Resistance:20m Ω (max)

Insulation Resistance:1000M Ω Min at 500V DC

Dielectric Strength:500V AC Per 1 Minute

Operating Temperature:-40℃ TO +105℃

MATERIALS:

Insulator:Nylon- 6T ,UL94V-0

Contact:Brass

Contact plated: Gold Over Nickel

Poles	Part No.	Dimension mm		
		A	B	C
6	B-3002N06P-0110	13.34	12.24	4.00
8	B-3002N08P-0110	15.34	14.24	6.00
10	B-3002N10P-0110	17.34	16.24	8.00
12	B-3002N12P-0110	19.34	18.24	10.00
14	B-3002N14P-0110	21.34	20.24	12.00
16	B-3002N16P-0110	23.34	22.24	14.00
18	B-3002N18P-0110	25.34	24.24	16.00
20	B-3002N20P-0110	27.34	26.24	18.00
24	B-3002N24P-0110	31.34	30.24	22.00
26	B-3002N26P-0110	33.34	32.24	24.00
30	B-3002N30P-0110	37.34	36.24	28.00
34	B-3002N34P-0110	41.34	40.24	32.00
40	B-3002N40P-0110	47.34	46.24	38.00
44	B-3002N44P-0110	51.34	50.24	42.00
50	B-3002N50P-0110	57.34	56.24	48.00

TOLERANCE TABLE

.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD				
CHECKED:	DATE:	TITLE: 300-2SMT-2*XP 平贴 (2.0贴面筒牛)				
DRAWN: SXA	DATE: 2019-06-29	CLIENT P/N		B-3002NXXP-0110		
		UNIT	mm	SCALE	free	☉
		FILE NO.	Ckmtw-300-0024	REV.	A	WY02