



1 2 3 4 5 6 7 8 9


G




F



E



D



C

SPECIFICATIONS

Current Rating: 1.5 Amps
 Insulation Resistance: $1000M\Omega$, Min
 Contact Resistance: $20m\Omega$, Max
 Withstanding Voltage: AC 500V
 Operation Temperature: -40° to $+105^\circ$
 Contact Material: Brass
 Standard: PA6T
 Insulator Material: Polyester (UL 94V-0)
 Contact Plating: Gold Flash
 Max. Processing Temp: 240° C for 30–60 seconds
 $(260^\circ$ C for 5 seconds)

B

A

SH 首韩®		深圳市首韩科技有限公司				
UNLESS OTHERWISE SPECIFIED TOLERANCE		DRAWN NAME: SH-JN2.0-2-2P-W-H.4				
X : ± 0.30	X° : $\pm 5^\circ$	SIZE	A4	SCALE	N:1	PROUCT NO.
X. X : ± 0.25	X. X° : $\pm 1^\circ$	REV	A	UNIT	mm	PROJECT
X. XX : ± 0.20	X. XX° : $\pm 0.5^\circ$	DRAW:	李春风	CHECKED:	钟华华	APPROVED:
			2022/04/30		2022/04/30	罗孝金
						PAGE 1/1

1 2 3 4 5 6 7 8 9