



REV.	MATTER	APP.	DATE
A			



NOTE:

1.MATERIAL:

a.HOUSING:THERMOPLASTIC GLASS FIBRE UL94V-0

b.CONTACT:PHOSPHOR BRONZE

(SURFACE PLATING:A*u")

SEE ORDERING INFORMATION

2.ELECTRIC:



a.CONTACT RESISTANCE: 30 MILLIOHMS MAX

b.INSULATION RESISTANCE: 1000 MEGA OHMS MIN

c.DIELECTNIC VOLTAGE: 750V AC ONE SEC LEVEL

d.OPERATING TEMPERATURE: -55°C~ +85°C

ORDERING INFORMATION



TOLERANCE		Tolerance: Unless otherwise specified			
LINEAR	ANGLE	3	TERMINAL-2	PHOSPHOR BRONZE	Au-Plated
		2	TERMINAL-1	PHOSPHOR BRONZE	Au-Plated
		1	HOUSING	PPS	BROWN
		NO.	PART NAME	MATERIAL	COLOR/FINISHED



深圳市连欣科技有限公司

Shenzhen City Lianxin Technology Co., Ltd

日期DATE	单位UNITS	审核CHECK	PART NO:
2023. 12. 25	mm		XDCR-1220-006/007
比例SCALE	制图 DRAW	设计DESIGN	TITLE:
1/1			BS-CR1220 贴片镀金2脚电池座子