







PC Board Layout
Component Side Shown

- 说明:
1. 材质:
胶芯: PBT, UL94V-0; COLOR; BLACK
端子: C5191
外壳: C2680
 2. 电镀说明:
端子: 镍底, 镀金G.F
外壳: 表面镀镍
 3. 性能说明:
 - 1) 电压: 150VACRMS.
 - 2) 额定电流: 1.5A.
 - 3) 接触电阻: 40mΩ Max.
 - 4) 绝缘电阻: 500MΩ MIN.
 - 5) 绝缘耐压: 1000VAC.
 - 6) 工作温度: -25° C TO +85° C.
 - 7) 耐久性: 500 Mating Cycles MIN.

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD					
CHECKED:	DATE:	TITLE: RJ45-10P/8C 59A-1*2 弯插 带屏蔽 带灯左黄右绿 无弹					
DRAWN: ZYJ	DATE: 2020-07-10	PART. NO.		R-RJ45R08P-C203			
		UNIT	mm	SCALE	free		
		FILE NO.	Ckmtw-RJ45-0413	REV.	A	HY04	