





客户确认

日期



PCB LAYOUT/TOP VIEW

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

说明 (NOTES):

1. 材质 (MATERIAL):

胶芯 (HOUSING): LCP, UL94V-0; COLOR: BLACK

端子 (CONTACT): PHOSPHOR BRONZE

外壳 (SHELL): BRASS

2. 电镀说明 (PLATING):

端子 (CONTACT): SELECTING GOLD $Fu \sim 50u''$ PLATING NICKEL

外壳 (SHELL): PLATING NICKEL

3. 电气性能 (ELECTRICAL):

1) 额定电压 (VOLTAGE RATING): 150VAC RMS.

2) 额定电流 (CURRENT RATING): 1.5A.

3) 接触电阻 (CONTACT RESISTANCE): $40m\Omega$ Max.

4) 绝缘电阻 (INSULATION RESISTANCE): 500 MEGOHMS MIN @ 500V DC

5) 绝缘耐压 (DIELECTRIC WITHSTANDING RESISTANCE): 1000V AC RMS 50Hz. 1MIN.

4. 机械性能 (MECHANICAL):

耐久性 (DURABILITY): 500 Mating Cycles MIN.

5. 环境温度 (ENVIRONMENTAL):

1) 存储温度 (STORAGE): -40°C TO 85°C

2) 工作温度 (OPERATION): -25°C TO $+85^{\circ}\text{C}$.

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD						
CHECKED:	DATE:	TITLE: RJ45-8P/8C 56B SMT 卧贴 带柱 带屏蔽						
DRAWN: SXA	DATE: 2019-05-14	PART. NO.		R-RJ45M08P-B000				
		UNIT	mm	SCALE	free			
		FILE NO.		Ckmtw-RJ45-0104		REV.	A	HY04