



ROHS+REACH

NO.	DATE	DESCRIPTION	APPROVAL
X0	2025.07.17	NEW PRODUCT	



NOTES:

- 1.100% CONTINUNY TEST ANY OPEN OR MIS WIRE, SHORT OR INTERMITENCE ARE NOT PERMITTED
- 2.INSULATION RESISTANCE:20M OHMS MIN
- 3.CONDUCTOR RESISTANCE:1Ω MAX

					DRAWING:	TOLERANCE .X:=±0.50 .XX:=±0.30 .XXX:=±0.10 .X':=±2'	 CHIN-BAN electronics (H.K) co., ltd	
					Frank			
					CHECKED:		DESCRIPTION: Pitch1.0mm-4P to TIN L=200mm	
					yangjie			
					APPROVAL:	UNIT: mm	CUSTOMER:	REV: X0
						SCALE:N/A	CUSTOMER P/N:	
						SHEET:1/1	DRAWING NO: P1.00-4P-01	SIZE: A4
③	TERMINAL	Pitch1.0mm crimp terminal materials: phosphorous bronze tin-plated AWG#28~#32	4PCS					
②	HOUSING	Pitch1.0mm 4Pin housing materials:white pa66	1PCS					
①	WIRE	UL1571 28AWG(7/0.127TS) 80°C 30V insulation:PVC OD:0.9mm	4PCS					
ITEM	TITLE	SPECIFICATION	Q'TY	CHIN-BAN P/N				