





ROHS+REACH

REV.	DATE	DESCRIPTION	APPROVAL
X0	2025.07.17	NEW PRODUCT	

P1

P2



NOTES:
1.100% CONTINUNY TEST ANY OPEN OR MIS WIRE, SHORT OR INTERMITENCE ARE NOT PERMITTED
2.INSULATION RESISTANCE:20M OHMS MIN
3.CONDUCTOR RESISTANCE:1Ω MAX

ITEM	TITLE	SPECIFICATION	Q'TY	CHIN-BAN P/N
③	HOUSING	SINGLE ROW SOCKET PITCH:2.0mm*4PIN MATERIALS:PA66 WHITE	1PCS	
②	TERMINAL	PITCH2.0MM CRIMP TERMINAL MATERIALS:PHOSPHOROUS BRONZE TIN-PLATED 24-28AWG	4PCS	
①	WIRE	UL1007 26AWG(7/0.16TS) 80°C 300V 绝缘:PVC OD:1.3mm	4PCS	

DRAWING:	TOLERANCE .X:=±0.50 .XX:=±0.30 .XXX:=±0.10 .X':=±2'	 CHIN-BAN electronics (H.K) co., ltd	
Frank		DESCRIPTION: Pitch2.00mm-4P to TIN L=200mm	
CHECKED:	yangjie	UNIT: mm	CUSTOMER:
APPROVAL:		SCALE:N/A	CUSTOMER P/N:
		SHEET:1/1	DRAWING NO: P2.00-4P-01
			REV: X0
			DEF. UK
			SIZE:A4