




BOTTOM VIEW



PCB LAYOUT

NOTES:

MATERIAL:

1. HOUSING MATERIAL : GLASS FILLED POLYESTER UL94V-0.
2. CONTACT MATERIAL : PHOSPHOR BRONZE $\phi=0.45\text{mm}$.
3. PLATING : GOLD PLATING $\text{Fu} \sim 50\mu\text{m}$ OVER NICKEL

ELECTRICAL:

1. VOLTAGE RATING : 125 VAC RMS.
2. CURRENT RATING : 1.5 AMP.
3. CONTACT RESISTANCE : 30 MILLIOHMS MAX.
4. INSULATION RESISTANCE : 500 MEGOHMS MIN @ 500V DC .
5. DIELECTRIC WITHSTANDING RESISTANCE : 1000V AC RMS 50Hz. 1MIN.

MECHANICAL:

1. DURABILITY : 750 CYCLES MIN.
2. PCB RETENTION PRE-SOLDER : 1 LB MIN.

ENVIRONMENTAL:

1. STORAGE : -40°C TO 85°C .
2. OPERATION : -25°C TO 85°C .

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRY CO., LTD					
CHECKED:	DATE:	TITLE: RJ45-10P/10C 56B-1*2 弯插 带屏蔽带弹 脚前3.05					
DRAWN: LYF	DATE: 2018-09-25	PART. NO.		R-RJ45R10P-B200			
		UNIT	mm	SCALE	free		
		FILE NO.	Ckmtw-RJ45-0411	REV.	A	HY04	

TOLERANCE TABLE

.0	± 0.30
.00	± 0.20
.000	± 0.05