






RoHS



RECOMMENDED P.C.B LAYOUT

目錄
MAPX

設 變 內 容
MODIFICATION

日 期
DATE

电气特性:Electrical:

1. 额定电流: Current Rating

5A/contact terminal

2. 额定电压: Voltage Rating

30V DC

3. 接触阻抗:Contact Resistance

30 milliohms MAX

4. 耐电压:Dielectnic Withstanding Voitage:

500 V AC AT Sea Level

5. 绝缘阻抗:Insulation Resistance:

1000MEGA ohms MIN

物理性能:Mechanical:

1. 插拔力: Cnnector Mate and Unmate Force

Mate force:3.57kgf (MAX)

Unmate force:0.7kgf (MIN)

2. 端子保持力: Terminal Retenion

1.0kgf (MIN)

3. 寿命: 1500次

原材料:Material:

1. 塑胶:Housing:pbt /lcp

2. 端子:Contact:Copper Alloy C2680

3. 外壳:Shell:SPCC/c2680

电镀:Finish:

1. 端子Contact: Au G/F u" Plated on contact area

Tin50u" Plated on solder area

Nickel 50u" Plated underplating over all.

2. 外壳Shell: Nickel 50u"Min plating over all.

3. Temperature Range:-55° C to +85° C

产品图

PRODUCT CHART DWG

深圳市精拓金电子有限公司

Pin NUMBER SIGNAL NAME

1 VBUS

2 D-

3 D+

4 GND

公差一览表

TOLERANCE UNLESS OTHERWISE

X. ±0.35 X'. ±5'

.X ±0.30 .X'. ±2'

.XX ±0.25 .XX'. ±1'

.XXX ±0.10 .XXX'. ±0.5'

单位
UNITS

MM

制图
DRAWING

L S S

产品料号
PRODUCT PART NO.

908-161A1161D30200

比例
SCALE

1:1

审核
CHKD

G Z F

产品名称
PRODUCT NO.

AF10.0A款大电流前两脚6.3无
边铁壳PBT紫胶6.3DIP G-0745

日期
DATE

2021/03/10

核准
APPD

黄国荣

角法
VIEW

版本
VER

AO