






PC BOARD LAYOUT
THICKNESS=1.6MM

说明 (NOTES):

1. 材质 (MATERIAL):

胶芯 (HOUSING): PBT, UL94V-0; COLOR: BLACK

端子 (CONTACT): PHOSPHOR BRONZE

2. 电镀说明 (PLATING):

端子 (CONTACT): SELECTING GOLD $Fu \sim 50u''$ PLATING NICKEL

3. 电气性能 (ELECTRICAL):

1) 额定电压 (VOLTAGE RATING): 150VACRMS.

2) 额定电流 (CURRENT RATING): 1.5A.

3) 接触电阻 (CONTACT RESISTANCE): $40m\Omega$ Max.

4) 绝缘电阻 (INSULATION RESISTANCE): 500 MEGOHMS MIN
@ 500V DC

5) 绝缘耐压 (DIELECTRIC WITHSTANDING RESISTANCE):
1000V AC RMS 50Hz. 1MIN.

4. 机械性能 (MECHANICAL):

耐久性 (DURABILITY): 500 Mating Cycles MIN.

5. 环境温度 (ENVIRONMENTAL):

1) 存储温度 (STORAGE): -40°C TO 85°C

2) 工作温度 (OPERATION): -25°C TO $+85^{\circ}\text{C}$.

TOLERANCE TABLE

.0	± 0.30
.00	± 0.20
.000	± 0.05

APPROVED:	DATE:	C kmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRY CO., LTD			
CHECKED:	DATE:	TITLE: RJ11-4P/4C 5721 弯插 全塑 带耳 黑色			
DRAWN: HCY	DATE: 2014-08-13	PART. NO.	R-RJ11R04P-A001		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-RJ11-0087	REV.	A HY04