







PC Board Layout
Component Side Shown

NOTES:

MATERIAL:

1. HOUSING MATERIAL : GLASS FILLED POLYESTER UL94V-0.
2. CONTACT MATERIAL : PHOSPHOR BRONZE $\phi=0.45\text{mm}$.
3. PLATING : GOLD PLATING $\text{Fu}^{\circ}\sim 50\mu^{\circ}$ OVER NICKEL

ELECTRICAL:

1. VOLTAGE RATING : 125 VAC RMS.
2. CURRENT RATING : 1.5 AMP.
3. CONTACT RESISTANCE : 30 MILLIOHMS MAX.
4. INSULATION RESISTANCE : 500 MEGOHMS MIN @ 500V DC .
5. DIELECTRIC WITHSTANDING RESISTANCE : 1000V AC RMS 50Hz. 1MIN.

MECHANICAL:

1. DURRABILITY : 750 CYCLES MIN.
2. PCB RETENTION PRE-SOLDER : 1 LB MIN.

ENVIRONMENTAL:

1. STORAGE : -40°C TO 85°C .
2. OPERATION : -25°C TO 85°C .

TOLERANCE TABLE	
.0	± 0.30
.00	± 0.20
.000	± 0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRY CO., LTD			
CHECKED:	DATE:	TITLE: RJ11-6P/6C 56B 弯插 全塑 带耳H:18 黑色			
DRAWN: LYF	DATE: 2018-09-25	PART. NO.		R-RJ11R06P-A012	
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-RJ11-0086	REV.	A HY04