


ROHS+REACH

REV.	DATE	DESCRIPTION	APPROVAL
X0	2025.07.17	NEW PRODUCT	



NOTES:

- 1.100% CONTINUNY TEST ANY OPEN OR MIS WIRE, SHORT OR INTERMITENCE ARE NOT PERMITTED
- 2.INSULATION RESISTANCE:20M OHMS MIN
- 3.CONDUCTOR RESISTANCE:1Ω MAX

ITEM	TITLE	SPECIFICATION	Q'TY	CHIN-BAN P/N
③	TERMINAL	Pitch:1.5mm crimping terminal phosphor bronze tin-plated 26-28AWG	2PCS	
②	HOUSING	Single row socket pitch:1.5mm*2Pin PA66 white	1PCS	
①	WIRE	UL1571 28AWG(7/0.127TS) 80°C 30V insulation:PVC OD:0.9mm	2PCS	

DRAWING:	TOLERANCE .X:=±0.50 .XX:=±0.30 .XXX:=±0.10 .X':=±2'	 CHIN-BAN electronics (H.K) co., ltd	
Frank			
CHECKED:		DESCRIPTION: Pitch1.50mm-2P to TIN L=200mm	
yangjie			
APPROVAL:	UNIT: mm	CUSTOMER:	REV: X0
	SCALE:N/A	CUSTOMER P/N:	DEF. UK
	SHEET:1/1	DRAWING NO: P1.50-2P-01	SIZE:A4