







PC Board Layout
Component Side Shown

NOTES:

MATERIAL:

- | | |
|--------------------|--|
| 1.HOUSING MATERIAL | :GLASS FILLED POLYESTER UL94V-0. |
| 2.CONTACT MATERIAL | :PHOSPHOR BRONZE $\phi 0.45\text{mm}$. |
| 3.PLATING | :GOLD PLATING $\text{Fu}^{\sim} 50\mu^{\sim}$ OVER NICKEL. |

ELECTRICAL:

- | | |
|--------------------------------------|------------------------------|
| 1.VOLTAGE RATING | :125 VAC RMS. |
| 2.CURRENT RATING | :1.5 AMP. |
| 3.CONTACT RESISTANCE | :30 MILLIOHMS MAX. |
| 4.INSULATION RESISTANCE | :500 MEGOHMS MIN @ 500V DC . |
| 5.DIELECTRIC WITHSTANDING RESISTANCE | :1000V AC RMS 50Hz. 1MIN. |

MECHANICAL:

- | | |
|----------------------------|------------------|
| 1.DURRABILITY | :750 CYCLES MIN. |
| 2.PCB RETENTION PRE-SOLDER | :1 LB MIN. |

ENVIRONMENTAL:

- | | |
|--------------|----------------------------------|
| 1. STORAGE | : -40 $^{\circ}$ ~+85 $^{\circ}$ |
| 2. OPERATION | : -25 $^{\circ}$ ~+85 $^{\circ}$ |

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRY CO., LTD			
CHECKED:	DATE:	TITLE: 网口插座 RJ45-8P/8C 59B-2*1 双胞胎 弯插 全塑 黑色			
DRAWN: W. J. B	DATE: 2024-06-21	PART. NO.	R-RJ45R08P-A205		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-RJ45-0393	REV.	A HY04

TOLERANCE TABLE

. 0	± 0.30
. 00	± 0.20
. 000	± 0.05