




ROHS+REACH

REV.	DATE	DESCRIPTION	APPROVAL
X0	2025.07.17	NEW PRODUCT	

P1

P2

200±5


Tin 3.0±0.5

红
黄
蓝
白
黑

1
2
3
4
5

②③

①



NOTES:

- 1.100% CONTINUNY TEST ANY OPEN OR MIS WIRE, SHORT OR INTERMITENCE ARE NOT PERMITTED
- 2.INSULATION RESISTANCE:20M OHMS MIN
- 3.CONDUCTOR RESISTANCE:1Ω MAX

ITEM	TITLE	SPECIFICATION	Q'TY	CHIN-BAN P/N
③	HOUSING	Single row socket pitch:2.5mm*5Pin PA66 white	1PCS	
②	TERMINAL	Pitch:2.5mm crimping terminal phosphor bronze tin-plated 22-28AWG	5PCS	
①	WIRE	UL1007 24AWG 80℃ 300V INSULATION:PVC OD:1.4MM	5PCS	

DRAWING:	TOLERANCE .X:=±0.50 .XX:=±0.30 .XXX:=±0.10 .X*:=±2°	 CHIN-BAN electronics (H.K) co., ltd	
Frank		DESCRIPTION: Pitch2.50mm-5P to TIN L=200mm	
CHECKED: yangjie		UNIT: mm	REV: X0
APPROVAL:		CUSTOMER P/N:	DEF. UK
		DRAWING NO: P2.50-5P-01	SIZE:A4