





RoHS2.0+REACH



■SPEC.:

- Rated Voltage:125V AC,DC
- Rated Current:1A AC,DC
- Withstand Voltage:500V AC/minute
- Contact Resistance:20mΩ max
- Insulation Resistance:100MΩ min
- Temperature Range:-25℃~+85℃

■Material:

- Insulator:PA66 UL94V-0
- Color:White

| Poles | Dimensions (mm) |       |       |
|-------|-----------------|-------|-------|
|       | A               | B     | C     |
| 02    | 1.25            | 2.95  | 4.25  |
| 03    | 2.50            | 4.20  | 5.50  |
| 04    | 3.75            | 5.45  | 6.75  |
| 05    | 5.00            | 6.70  | 8.00  |
| 06    | 6.25            | 7.95  | 9.25  |
| 07    | 7.50            | 9.20  | 10.50 |
| 08    | 8.75            | 10.45 | 11.75 |
| 09    | 10.00           | 11.70 | 13.00 |
| 10    | 11.25           | 12.95 | 14.25 |
| 11    | 12.50           | 14.20 | 15.50 |
| 12    | 13.75           | 15.45 | 16.75 |
| 13    | 15.00           | 16.70 | 18.00 |
| 14    | 16.25           | 17.95 | 19.25 |
| 15    | 17.50           | 19.20 | 20.50 |
| 16    | 18.75           | 20.45 | 21.75 |

|     |      |             |         |
|-----|------|-------------|---------|
| 5.0 |      |             |         |
| 4.0 |      |             |         |
| 3.0 |      |             |         |
| 2.0 |      |             |         |
| 1.0 |      |             |         |
| NO. | DATE | DESCRIPTION | DRAWING |

DRAWING:  
Frank  
CHECKED:  
yangjie  
APPROVAL:

GENERAL TOLERANCE  
.X:=±0.30 .X':=±2°  
.XX:=±0.25 .XX':=±1°  
.XXX:=±0.15 .XXX':=±0.5°  
UNIT: MM PROJECTION:  
SCALE: 1:1  
SHEET: 1/1

**CHIN-BAN**  
Electronic Technology

DESCRIPTION: Housing P1.25mm

PART NO: **WF125-04P-004**

OLD CODE:

DRAWING NO:

REV: 1.0

SIZE: A4