






RoHS2.0+REACH



■SPEC.

- Voltage Rating:150V AC/DC
- Current Rating:1A AC/DC
- Withstanding Voltage:500V AC/minute
- Contact Resistance:20mΩ max
- Insulation Resistance:500MΩ min
- Temperature Range:-35°C~+85°C

■Material:

- Insulator:PA66 UL94V-0
- Color:White

Poles	Dimensions(mm)			
	A	B	C	D
02	1.25	4.40	2.75	1.10
03	2.50	5.65	4.00	1.95
04	3.75	6.90	5.25	2.60
05	5.00	8.15	6.50	3.20
06	6.25	9.40	7.75	3.20
07	7.50	10.65	9.00	3.20
08	8.75	11.90	10.25	3.20
09	10.00	13.15	11.50	3.20
10	11.25	14.40	12.75	3.20
11	12.50	15.65	14.00	4.70
12	13.75	16.90	15.25	4.70
13	15.00	18.15	16.50	4.70
14	16.25	19.40	17.75	4.70
15	17.50	20.65	19.00	4.70
20	23.75	26.90	25.25	4.70
25	30.00	33.15	31.50	5.70
30	36.25	39.40	37.75	5.70

5.0				DRAWING:	GENERAL TOLERANCE			
4.0				Frank	.X:=±0.30	.X':=±2°		
3.0				CHECKED:	.XX:=±0.25	.XX':=±1°	DESCRIPTION: Housing P1.25mm	
2.0				yangjie	.XXX:=±0.15	.XXX':=±0.5°		
1.0				APPROVAL:	UNIT: MM	PROJECTION:	PART NO: WF125-10P-001	REV: 1.0
NO.	DATE	DESCRIPTION	DRAWING		SCALE: 1:1		OLD CODE:	SIZE: A4
					SHEET: 1/1		DRAWING NO:	