







NOTES:

MATERIAL :

- | | |
|--------------------|--|
| 1.HOUSING MATERIAL | :GLASS FILLED POLYESTER UL94V-0. |
| 2.CONTACT MATERIAL | :PHOSPHOR BRONZE ϕ 0.46mm. |
| 3.PLATING | :GOLD PLATING OVER NICKEL. |
| 4.SHIELD | :0.23mm THICKNESS COPPER ALLOY WITH NICKEL PLATED. |

ELECTRICAL:

- | | |
|--------------------------------------|------------------------------|
| 1.VOLTAGE RATING | :125 VAC RMS. |
| 2.CURRENT RATING | :15 AMP. |
| 3.CONTACT RESISTANCE | :30 MILLIOHMS MAX. |
| 4.INSULATION RESISTANCE | :500 MEGOHMS MIN @ 500V DC . |
| 5.DIELECTRIC WITHSTANDING RESISTANCE | :1000V AC RMS 50Hz. 1MIN. |

MECHANICAL:

- | | |
|----------------------------|------------------|
| 1.DURRABILITY | :750 CYCLES MIN. |
| 2.PCB RETENTION PRE-SOLDER | :1 LB MIN. |

ENVIRONMENTAL:

- | | |
|-------------|-------------|
| 1.STORAGE | : -40℃~+85℃ |
| 2.OPERATION | : -25℃~+85℃ |

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD										
CHECKED:	DATE:	TITLE: 网口插座 RJ45-8P/8C 59B-2*4 八口 双排弯插 带屏蔽 无灯无弹										
DRAWN: L. YUN	DATE: 2018-12-19	PART. NO.			R-RJ45R08P-B801							
		UNIT		mm		SCALE		free		 		
		FILE NO.		Ckmtw-RJ45-0246			REV.		A	HY04		

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05