






RoHS2.0+REACH



Circuits 1



- SPEC.:
- Rated Voltage:200V AC,DC
 - Rated Current:1A AC,DC
 - Withstand Voltage:500V AC/minute
 - Contact Resistance:40mΩ max
 - Insulation Resistance:100MΩ min
 - Temperature Range:-25℃~+85℃
- Material:
- Insulator:PA66 UL94-V0
 - Color:BK-Black

Poles	Dimensions(mm)				
	A	B	C	D	E
02	6.00	1.25	3.80		3.20
03	7.25	2.50	5.05		4.45
04	8.50	3.75	6.30		5.70
05	9.75	5.00	7.55		6.95
06	11.00	6.25	8.80		8.20
08	13.50	8.75	11.30	7.58	10.70
10	16.00	11.25	13.80	10.10	13.20
15	22.25	17.50	20.05	16.38	19.45
20	28.50	23.75	26.30	22.70	25.70
25	34.75	30.00	32.55	28.95	31.95
30	41.00	36.25	38.80	35.25	38.20

5.0				DRAWING:	GENERAL TOLERANCE		CHIN-BAN Electronic Technology	
4.0				Frank	.X:=±0.30	.X*:=±2°		
3.0				CHECKED:	.XX:=±0.25	.XX*:=±1°	DESCRIPTION: Housing P1.25mm	
2.0				yangjie	.XXX:=±0.15	.XXX*:=±0.5°		
1.0				APPROVAL:	UNIT: MM	PROJECTION:	PART NO: WF125-20P-003	REV: 1.0
NO.	DATE	DESCRIPTION	DRAWING		SCALE: 1:1		OLD CODE:	SIZE: A4
					SHEET: 1/1		DRAWING NO:	