


## ROHS+REACH

| NO. | DATE       | DESCRIPTION | APPROVAL |
|-----|------------|-------------|----------|
| X0  | 2025.07.17 | NEW PRODUCT |          |
|     |            |             |          |



NOTES:

- 1.100% CONTINUITY TEST ANY OPEN OR MIS WIRE, SHORT OR INTERMITTENCE ARE NOT PERMITTED
- 2.INSULATION RESISTANCE:20M OHMS MIN
- 3.CONDUCTOR RESISTANCE:1Ω MAX

|      |          |                                                                                   |      |              |                     |                                                                                       |                                                                                                                                     |          |
|------|----------|-----------------------------------------------------------------------------------|------|--------------|---------------------|---------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------|----------|
|      |          |                                                                                   |      |              | DRAWING:            | TOLERANCE<br>.X:=±0.50<br>.XX:=±0.30<br>.XXX:=±0.10<br>.X':=±2"                       |  <b>CHIN-BAN</b><br>electronics (H.K) co., ltd |          |
|      |          |                                                                                   |      |              | Frank               |                                                                                       |                                                                                                                                     |          |
| ③    | TERMINAL | Pitch1.25mm crimp terminal materials:<br>phosphorous bronze tin-plated AWG#28~#32 | 3PCS |              | CHECKED:<br>yangjie |  | DESCRIPTION:<br>Pitch1.25mm-3P to TIN L=200mm                                                                                       |          |
| ②    | HOUSING  | Pitch1.25mm 3Pin housing materials:white pa66                                     | 1PCS |              | APPROVAL:           | UNIT: mm                                                                              | CUSTOMER:                                                                                                                           | REV: X0  |
| ①    | CABLE    | UL1571 28AWG(7/0.127TS) 80°C 30V insulation:PVC OD:0.9mm                          | 3PCS |              |                     | SCALE:N/A                                                                             | CUSTOMER P/N:                                                                                                                       | DEF. UK  |
| ITEM | TITLE    | SPECIFICATION                                                                     | Q'TY | CHIN-BAN P/N |                     | SHEET:1/1                                                                             | DRAWING NO: P1.25-3P-01                                                                                                             | SIZE: A4 |