




目錄 MAPX	設 變 內 容 MODIFICATION	日期 DATE

电气特性:Electrical:

1. 额定电流: Current Rating
5A/contact terminal
2. 额定电压: Voltage Rating
30V DC
3. 接触阻抗:Contact Resistance
30 milliohms MAX
4. 耐电压:Dielectnrc Withstanding Voitage:
500 V AC AT Sea Levcl
5. 绝缘阻抗:Lnsulation Resistance:
1000MEGA ohms MIN

物理性能:Mechanical:

1. 插拔力: Cnnector Mate and Unmate Force
Mate force:3. 57kgf (MAX)
Unmate force:0. 7kgf (MIN)
2. 端子保持力: Terminal Retenion
1. 0kgf (MIN)
3. 寿命: 1500次

原材料:Material:

1. 塑胶:Housing:pbt /lcp
2. 端子:Contact:Copper Alloy C2680
3. 外壳:Shell:SPCC/c2680

电镀:Finish:

1. 端子Contact: Au G/F u" Plated on contact area
Tin50u" Plated on solder area
Nickel 50u" Plated underplating over all.
2. 外壳Shell: Nickel 50u"Min plating over all.
3. Temperature Range:-55° C to +85° C

产品图 PRODUCT CHART DWG				深圳市精拓金电子有限公司							
Pin NUMBER	SIGNAL NAME	公差一览表 TOLERANCE UNLESS OTHERWISE		单位 UNITS	MM	制图 DRAWING	L S S	产品料号 PRODUCT PART NO.	908-161A1111D30200		
1	VBUS	X.	±0.35	X'.	±5'	比例 SCALE	1:1	审核 CHKD	G Z F	产品名称 PRODUCT NO.	AF10.0A款大电流前两脚6.3元 边铁壳PBT橙胶6.3DIP G-0862
2	D-	.X	±0.30	.X*	±2'	日期 DATE	2021/03/10	核准 APPD	黄国荣	角法 VIEW	⊕ ⊖
3	D+	.XX	±0.25	.XX*	±1'	版本 VER					A0
4	GND	.XXX	±0.10	.XXX*	±0.5'						