




RECOMMEND PULG




PCB. WELDING DRAWING (TOLERANCE: ± 0.05)



Main technical performance

<i>PIN</i>	<i>MODEL</i>
$\phi 1.00$	<i>DC031A-B10</i>
$\phi 1.30$	<i>DC031A-B13</i>

4	TERMINAL	1	BRASS	MB:CuSn PLATED
3	HOUSING	1	PPA	BLACK
2	TIP SPRING	1	PHOSPHOR BRONZE	MB:CuSn PLATED
1	CENTER PIN	1	BRASS	MB:CuSn PLATED
LTR	PART NAME	QTY	MATERIAL	REMARK

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTCONN Shenzhen Huamington Electronics Co., Ltd				
X. [°] ±0.30	X. [°] ±5°	PART NO.		TITLE:		
X.X [°] ±0.25	X.X [°] ±1°	DC031A-BN		DC SOCKET		
X.XX [°] ±0.15		DESIGN: James		CUSTOMER	SIZE	
MANUFACTURE DWG		CHED: Talen			A4	UNITS
		APPD: Sophia			SCALE	SHEET
					N:A	
					1/1	