







PCB LAYOUT



#### 说明 (NOTES):

##### 1. 材质 (MATERIAL):

胶芯 (HOUSING): PBT, UL94V-0; COLOR: BLACK

端子 (CONTACT): PHOSPHOR BRONZE

##### 2. 电镀说明 (PLATING):

端子 (CONTACT): SELECTING GOLD  $Fu \sim 50u''$  PLATING NICKEL

##### 3. 电气性能 (ELECTRICAL):

1) 额定电压 (VOLTAGE RATING): 150VACRMS.

2) 额定电流 (CURRENT RATING): 1.5A.

3) 接触电阻 (CONTACT RESISTANCE):  $40m\Omega$  Max.

4) 绝缘电阻 (INSULATION RESISTANCE): 500 MEGOHMS MIN @ 500V DC

5) 绝缘耐压 (DIELECTRIC WITHSTANDING RESISTANCE): 1000V AC RMS 50Hz. 1MIN.

##### 4. 机械性能 (MECHANICAL):

耐久性 (DURRABILITY): 500 Mating Cycles MIN.

##### 5. 环境温度 (ENVIRONMENTAL):

1) 存储温度 (STORAGE):  $-40^{\circ}\text{C}$  TO  $85^{\circ}\text{C}$

2) 工作温度 (OPERATION):  $-25^{\circ}\text{C}$  TO  $+85^{\circ}\text{C}$ .

TOLERANCE TABLE

|      |            |
|------|------------|
| .0   | $\pm 0.30$ |
| .00  | $\pm 0.20$ |
| .000 | $\pm 0.05$ |

|               |                     |                                                    |                 |       |        |
|---------------|---------------------|----------------------------------------------------|-----------------|-------|--------|
| APPROVED:     | DATE:               | C kmtw 深圳市灿科盟实业有限公司<br>CHANKEMENG INDUSTRYCO., LTD |                 |       |        |
| CHECKED:      | DATE:               | TITLE:<br>RJ45-8P/8C 5722 弯插 全塑 无耳18.1 黑色          |                 |       |        |
| DRAWN:<br>HCY | DATE:<br>2014-08-13 | PART. NO.                                          | R-RJ45R08P-A019 |       |        |
|               |                     | UNIT                                               | mm              | SCALE | free   |
|               |                     | FILE NO.                                           | Ckmtw-RJ45-0416 | REV.  | A HY04 |