







PC Board Layout
Component Side Shown

NOTES:

MATERIAL:

- | | |
|---------------------|---|
| 1. HOUSING MATERIAL | : GLASS FILLED POLYESTER UL94V-0. |
| 2. CONTACT MATERIAL | : PHOSPHOR BRONZE Ø0.45mm. |
| 3. PLATING | : GOLD PLATING 50u" OVER NICKEL. |
| 4. SHIELD | : 0.20mm THICKNESS COPPER ALLOY WITH NICKEL PLATED. |

ELECTRICAL:

- | | |
|---------------------------------------|------------------------------|
| 1. VOLTAGE RATING | : 125 VAC RMS. |
| 2. CURRENT RATING | : 1.5 AMP. |
| 3. CONTACT RESISTANCE | : 30 MILLIOHMS MAX. |
| 4. INSULATION RESISTANCE | : 500 MEGOHMS MIN @ 500V DC. |
| 5. DIELECTRIC WITHSTANDING RESISTANCE | : 1000V AC RMS 50Hz. 1MIN. |

MECHANICAL:

- | | |
|-----------------------------|-------------------|
| 1. DURRABILITY | : 750 CYCLES MIN. |
| 2. PCB RETENTION PRE-SOLDER | : 1 LB MIN. |

ENVIRONMENTAL:

- | | |
|--------------|---------------|
| 1. STORAGE | : -40°C~+85°C |
| 2. OPERATION | : -25°C~+85°C |

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRY CO., LTD					
CHECKED:	DATE:	TITLE: 网口插座 RJ45-8P/8C 59B-2*1 双层 弯插 带屏蔽 无灯带弹					
DRAWN: L. YUN	DATE: 2020-11-12	PART. NO.		R-RJ45R08P-B204			
		UNIT	mm	SCALE	free	⊕	≡
		FILE NO.	Ckmtw-RJ45-0217	REV.	A	HY00	