





RoHS2.0+REACH

■SPEC.:

- Rated Voltage: 250V AC,DC
- Rated Current: 2A AC,DC
- Withstand Voltage: 800V AC/minute
- Contact Resistance: 20mΩ max
- Insulation Resistance: 1000MΩ min
- Temperature Range: -25°C~+85°C

■Material:

- Insulator:PA66 UL94V-0
- Color:White



Poles	Dimensions(mm)				
	A	B	C	D	E
2X03P	6.60	8.80	4.00	3.10	1.50
2X04P	8.60	10.80	6.00	5.00	2.60
2X05P	10.60	12.80	8.00	6.20	3.50
2X06P	12.60	14.80	10.00	8.20	5.50
2X07P	14.60	16.80	12.00	9.80	7.20
2X08P	16.60	18.80	14.00	10.20	7.50
2X09P	18.60	20.80	16.00	14.20	11.50
2X10P	20.60	22.80	18.00	14.20	11.50
2X11P	22.60	24.80	20.00	14.20	11.50
2X12P	24.60	26.80	22.00	16.20	13.60
2X13P	26.60	28.80	24.00	16.20	13.60
2X14P	28.60	30.80	26.00	16.20	13.60
2X15P	30.60	32.80	28.00	16.20	13.60
2X16P	32.60	34.80	30.00	16.20	13.60
2X17P	34.60	36.80	32.00	16.20	13.60
2X18P	36.60	38.80	34.00	16.20	13.60
2X19P	38.60	40.80	36.00	16.20	13.60
2X20P	40.60	42.80	38.00	16.20	13.60

5.0			
4.0			
3.0			
2.0			
1.0			
NO.	DATE	DESCRIPTION	DRAWING

DRAWING:
Frank
CHECKED:
yangjie
APPROVAL:

GENERAL TOLERANCE

.X:=±0.30 .X*:=±2°
.XX:=±0.25 .XX*:=±1°
.XXX:=±0.15 .XXX*:=±0.5°

UNIT: MM

PROJECTION:

SCALE: 1:1



SHEET: 1/1

CHIN-BAN
Electronic Technology

DESCRIPTION: Housing P2.00mm

PART NO: **WF200-16P-002**

REV: 1.0

OLD CODE:

DRAWING NO:

SIZE: A4