







RoHS2.0+REACH



3P



2P



■SPEC.:

- Rated Voltage:125V AC,DC
- Rated Current:1A AC,DC
- Withstand Voltage:250V AC/minute
- Contact Resistance:20mΩ max
- Insulation Resistance:100MΩ min
- Temperature Range:-25℃~+85℃

■Material:

- Insulator:PA66 UL94V-0
- Color:White

Poles	Dimensions(mm)		
	A	B	C
02	1.25	2.72	5.72
03	2.50	3.97	6.97
04	3.75	5.22	8.22
05	5.00	6.47	9.47
06	6.25	7.72	10.72
07	7.50	8.97	11.97
08	8.75	10.22	13.22
09	10.00	11.47	14.47
10	11.25	12.72	15.72
11	12.50	13.97	16.97
12	13.75	15.22	18.22
14	16.25	17.72	20.72
15	17.50	18.97	21.97
16	18.75	20.22	23.22
20	23.75	25.22	28.22
30	36.25	37.72	40.72

5.0				DRAWING:	GENERAL TOLERANCE		CHIN-BAN Electronic Technology	
4.0				Frank	.X:=±0.30	.X*:=±2°		
3.0				CHECKED:	.XX:=±0.25	.XX*:=±1°	DESCRIPTION: Housing P1.25mm	
2.0				yangjie	.XXX:=±0.15	.XXX*:=±0.5°		
1.0				APPROVAL:	UNIT: MM	PROJECTION:	PART NO: WF125-05P-005	REV: 1.0
NO.	DATE	DESCRIPTION	DRAWING		SCALE: 1:1		OLD CODE:	SIZE: A4
					SHEET: 1/1		DRAWING NO:	