



RoHS2.0+REACH



Circuit 1



03~20P

02P

■SPEC.:

- Voltage Rating: 50V AC/ DC
- Current Rating: 1A AC/ DC
- Withstanding Voltage: 500V AC/Minute
- Contact Resistance: 20mΩ max
- Insulation Resistance: 100MΩ min
- Temperature Range: -25°C~+85°C

■Material:

- Insulator: PA66 UL94V-0
- Color: White

Poles	Dimensions (mm)				
	A	B	C	D	E
02	1.00	3.00	2.40	1.75	3.00
03	2.00	4.00	3.40	2.75	4.00
04	3.00	5.00	4.40	2.75	4.00
05	4.00	6.00	5.40	2.75	4.00
06	5.00	7.00	6.40	2.75	4.00
07	6.00	8.00	7.40	2.75 (窄扣)	4.00 (窄扣)
08	7.00	9.00	8.40		
09	8.00	10.00	9.40		
10	9.00	11.00	10.40		
11	10.00	12.00	11.40	4.75 (宽扣)	6.00 (宽扣)
12	11.00	13.00	12.40		
13	12.00	14.00	13.40		
14	13.00	15.00	14.40		
15	14.00	16.00	15.40	4.75 (宽扣)	6.00 (宽扣)
16	15.00	17.00	16.40		
17	16.00	18.00	17.40		
18	17.00	19.00	18.40		
19	18.00	20.00	19.40		
20	19.00	21.00	20.40		

5.0				DRAWING:	GENERAL TOLERANCE		
4.0				Frank	.X: = ±0.30 .X*: = ±2°		
3.0				CHECKED:	.XX: = ±0.25 .XX*: = ±1°		
2.0				yangjie	.XXX: = ±0.15 .XXX*: = ±0.5°		
1.0				APPROVAL:	UNIT: MM PROJECTION:	DESCRIPTION: Housing P1.00mm	
NO.	DATE	DESCRIPTION	DRAWING		SCALE: 1:1	PART NO: WF100-06P-002	REV: 1.0
					SHEET: 1/1	OLD CODE:	SIZE: A4
						DRAWING NO:	

CHIN-BAN
Electronic Technology

DESCRIPTION: Housing P1.00mm
PART NO: WF100-06P-002
OLD CODE:
DRAWING NO:
REV: 1.0
SIZE: A4