







PC Board Layout
Component Side Shown

NOTES:

MATERIAL:

- | | |
|---------------------|---|
| 1. HOUSING MATERIAL | : GLASS FILLED POLYESTER UL94V-0. |
| 2. CONTACT MATERIAL | : PHOSPHOR BRONZE $\phi 0.45\text{mm}$. |
| 3. PLATING | : GOLD PLATING $\text{Fu} \sim 50\text{u}''$ OVER NICKEL. |

ELECTRICAL:

- | | |
|---------------------------------------|-------------------------------|
| 1. VOLTAGE RATING | : 125 VAC RMS. |
| 2. CURRENT RATING | : 1.5 AMP. |
| 3. CONTACT RESISTANCE | : 30 MILLIOHMS MAX. |
| 4. INSULATION RESISTANCE | : 500 MEGOHMS MIN @ 500V DC . |
| 5. DIELECTRIC WITHSTANDING RESISTANCE | : 1000V AC RMS 50Hz. 1MIN. |

MECHANICAL:

- | | |
|-----------------------------|-------------------|
| 1. DURRABILITY | : 750 CYCLES MIN. |
| 2. PCB RETENTION PRE-SOLDER | : 1 LB MIN. |

ENVIRONMENTAL:

- | | |
|--------------|---|
| 1. STORAGE | : $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$ |
| 2. OPERATION | : -25°C TO 80°C . |

TOLERANCE TABLE	
.0	± 0.30
.00	± 0.20
.000	± 0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: 网口插座 RJ45-8P/8C 59B-2*2 四口 弯插 全塑 黑色			
DRAWN: luli-liu	DATE: 2023-10-12	PART. NO.	R-RJ45R08P-A401		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-RJ45-0309	REV.	A HY04