





RoHS2.0+REACH



Section:A-A



■SPEC.:

- Rated Voltage:50V AC,DC
- Rated Current:1A AC,DC
- Withstand Voltage:500V AC/minute
- Contact Resistance:20mΩ max
- Insulation Resistance:100MΩ min
- Temperature Range:-25℃~+85℃

■Material:

- Insulator:PA66 UL94V-0
- Color: White

| Poles | Dimensions (mm) |       |       |
|-------|-----------------|-------|-------|
|       | A               | B     | C     |
| 02    | 1.00            | 3.00  | 2.40  |
| 03    | 2.00            | 4.00  | 3.40  |
| 04    | 3.00            | 5.00  | 4.40  |
| 05    | 4.00            | 6.00  | 5.40  |
| 06    | 5.00            | 7.00  | 6.40  |
| 07    | 6.00            | 8.00  | 7.40  |
| 08    | 7.00            | 9.00  | 8.40  |
| 09    | 8.00            | 10.00 | 9.40  |
| 10    | 9.00            | 11.00 | 10.40 |
| 11    | 10.00           | 12.00 | 11.40 |
| 12    | 11.00           | 13.00 | 12.40 |
| 13    | 12.00           | 14.00 | 13.40 |
| 14    | 13.00           | 15.00 | 14.40 |
| 15    | 14.00           | 16.00 | 15.40 |
| 16    | 15.00           | 17.00 | 16.40 |
| 17    | 16.00           | 18.00 | 17.40 |
| 18    | 17.00           | 19.00 | 18.40 |
| 19    | 18.00           | 20.00 | 19.40 |
| 20    | 19.00           | 21.00 | 20.40 |

|     |      |             |         |
|-----|------|-------------|---------|
| 5.0 |      |             |         |
| 4.0 |      |             |         |
| 3.0 |      |             |         |
| 2.0 |      |             |         |
| 1.0 |      |             |         |
| NO. | DATE | DESCRIPTION | DRAWING |

DRAWING:  
Frank  
CHECKED:  
yangjie  
APPROVAL:


GENERAL TOLERANCE

.X:=±0.30 .X\*:=±2°  
.XX:=±0.25 .XX\*:=±1°  
.XXX:=±0.15 .XXX\*:=±0.5°

UNIT: MM

PROJECTION:

SCALE: 1:1



SHEET: 1/1

**CHIN-BAN**  
Electronic Technology

DESCRIPTION: Housing P1.00mm

PART NO: **WF100-06P-003**

OLD CODE:

DRAWING NO:

REV: 1.0

SIZE: A4