








RoHs



PCB. WELDING DRAWING (TOLERANCE: ± 0.05)

Main technical performance	
Rated electrical load	DC 12V 2A
Contact resistance	$\leq 30m \Omega$
Insulation resistance	$\geq 100M \Omega$
Pressure resistance	AC 500V 1min
Insertion force	3-30N
Operating temperature range	-20C° ~+70C°
service life	5000cycles

PIN	MODEL
$\phi 1.0$	DC003B-A10
$\phi 1.3$	DC003B-A13

6	弹片	1	H62	镀银
5	插片	1	H62	镀银
4	平片	1	H62	镀银
3	中心针	1	H62	铜锡
2	盖板	1	PPA	黑
1	基座	1	PPA	黑
序号	名称	数量	材料	备注
GENERAL TOLERANCES UNLESS SPECIFIED		HMTCONN 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd		
X.* ± 0.30	X.* $\pm 5^\circ$	PART NO. DC003B-AN	TITLE: DC SOCKET	
X.X* ± 0.25	X.X* $\pm 1^\circ$			
X.XX* ± 0.15		DESIGN: James	CUSTOMER	SIZE A4
MANUFACTURE DWG		CHED: Talen		UNITS MM
		APPD: Sophia		SCALE N:A
				SHEET 1/1